

Search within category

GO

BUY NOW

DESIGN / INSTALL



PLF1M-M69

Pan-Ty® flag tie, flag, miniature cross section, 4.3 (109mm) length, .31 x .75 (7.9 x 19.1mm) marker write-on area, flame retardant nylon 6.6, ivory.

Specs

Packaging Details

Tools

Documents

★ Add to Favorites

Add to BOM

Material	Nylon 6.6
Application	General
Color	Ivory
Cross Section	Miniature
Locking Style	Locking
Plenum-Rated	No
Tool	GTS-E, GS2B, PTS, PPTS, STS2
Length In (mm)	4.30 (109)
Marker Type	Flag
CE Compliant	Yes
CSA Certified	Yes
UL Listed (File #E56854)	No
UL Recognized (File #E56854)	Yes
Bundle Diameter Range In. (mm)	0.06 (1.5) - 0.87 (22)
Continuous Use Temperature Range	-76°F (-60°C) - 212°F (100°C)
Installation Temperature	-4°F (-20°C) - 32°F (0°C)
Min. Loop Tensile Strength (Lbs.)	18
Min. Loop Tensile Strength (N)	80
Operating Temperature	-76°F (-60°C) - 212°F (100°C)
Part Features	Used to fasten and identify bundles at the same time, Can be custom imprinted
Thickness In (mm)	0.04 (1.1)
Width In (mm)	0.098 (2.5)
RoHS Compliancy Status	Compliant
Min. Order Qty.	1,000