



Part Number : [1301430273](#)
Product Description : Watertite Extreme Cordset,
10 Gauge SOOW, 3 Pole/4 Wire, Cordset, Length
30.48m (100.0'), NEMA L14-30, 125V/250V
Series Number : 130143
Status : Active
Product Category : Wiring Devices
Engineering Number : 28W74D104



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Wiring Devices
Series	130143
Description	Watertite Extreme Cordset, 10 Gauge SOOW, 3 Pole/4 Wire, Cordset, Length 30.48m (100.0'), NEMA L14-30, 125V/250V
Comments	125V and 250V
IP Rating	IP67
NEMA Configuration	NEMA L14-30
Product Name	Watertite Extreme
Specialty	N/A
Type	Cordset
UPC	78678871089

Agency

CSA	LR6837
UL	E38085

Electrical

Current - Maximum per Contact	30.0A
GFCI	No
Voltage - Maximum	125V / 250V

Physical

Cord Grip Body Size	F4 1"
Cord Type	12/3 SOOW
Flange	No
Flip Lid	No
Gender	Male-Female
Length	30.48m (100.0')
Lighted Connector	No
Locking Blade	Yes

Net Weight	777.000/kg
Poles	3-pole/4-wire
Receptacle Type	N/A

This document was generated on Sep 24, 2025