HellermannTyton

Technical data sheet

Article number:
115-00030 SpeedyTie (RTT750HR)

Product Group	Cable ties with quick release mechanism, parallel bundling
Product Family	SpeedyTie
Material	Polyamide 6.6, high impact modified, scan black (PA66HIR(S))
Colour	Black (BK)

Bundle Ø max.	210.0 mm
Bundle Ø min.	40.0 mm
Flammability	UL 94 HB
Length (L)	752.0 mm
Min.Tensile Strength	888 N
Operating Temperature	-40 °C to +80 °C
Package Content	5 pcs.
Package Content packed in	pack
Releasable Closure (Yes/No)	Yes
Thickness (T)	1.9 mm
Variant	Inside Serrated
Weight/Unit	0.022572 kg
Width (W)	13.0 mm

RoHS

created on 18. September 2026, 7:18 am

Technical changes and errors reserved. It's up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.