

Intel® Pentium® 4 Processor 3.06GHz
(Socket 478)
CPU Cooler

SAN ACE MC



General Specifications

- Material Frame: Plastics (Flammability: UL94V-0),
Impeller: Plastics (Flammability: UL94V-1) Heatsink: Aluminum (Core: Copper)
- Lead Wire ⊕yellow (Connector No.2 side) ⊖black (Connector No.1 side)
Sensor green (Connector No.3 side)
- Connector..... Molex 22-01-3037: P/N 2695-03RP
- Contact Molex P/N 5159PBT or equivalent
- Mass 450g

Specifications

Model No.	Rated Voltage [V]	Operating Voltage Range [V]	Rated Current [A]	Rated Speed [min ⁻¹]	θ_{c-a} Thermal Resistance [K/W]	SPL [dB(A)]	Operating Temperature [°C]	Life Expectancy [h]
109X9912T0S016	12	9 to 13.8	0.48	5,400	0.295	45	0 to +70	40,000
109X9912S0016				2,610	0.42	28		
				5,400	0.295	45		

Dimensions (Unit : mm)

