Brady is committed to providing the product solutions and guidance you need to return to work. See How

3" Core Metallized Glossy Polyester with 2 mil Adhesive Labels










Downloaded from Arrow.com.



Product Highlights:

Color:
Silver

Material:
Metallized Polyester

For Use with Printer:
BBP®81 Label Printer, BRADY IP® Series Label Printer, BradyPrinter i5100, BradyPrinter i7100, BRADYPRINTER PR Plus Series Label Printer, THT 3" Core Printer

Material Number:
B-434 (View Technical Data Sheet)

Label Properties:
Metallic Labels, Permanent Adhesive Labels

Choose your options:

Reset Options

1 Label/Tape Size

1 IN H X 2 IN W

Part Number:
THT-17-434-3

View All Options

ADD TO CART + —

Add To Favorites

People Also Viewed



BMP21-PLUS Camo Portable Label Printer - Limited Edition

Downloaded from Arrow.com.



3" Core Self-Laminating Vinyl Wire and Cable Labels



Thermal Transfer 1" Core R6000 Halogen Free Series Printer Ribbon



3" Core Metallized Glossy Polyester Rating Plate Labels

Need a different size? Customize it!

Calculate how many labels you can print with one ribbon

Request product certification

Overview

Metallized Polyester (B-434) labels are designed for applications that use barcodes, alphanumerics, graphic symbols and logos and require nameplate-like quality.

- Glossy, light gray finish gives labels a rating and serial plate appearance
- Labels are designed to withstand numerous solvents and variable temperatures when applied to various surfaces
- UL approved;CSA accepted
- Service temperature of -40 to 194° F (-40 to 90° C)

Downloaded from Arrow.com.

Specifications

Key Characteristics		165
	Product Number	30282
	UPC	662820302827
	UOM	Roll of 3000 Labels
	Quantity per Roll	3000
	Unit Price	/Label
	Trade Name	MetaLabel
	Brand Name	Brady®
		Mexico
		3919.10.2055
		EAR99

Dimensions	**Sign Size (H x W)**	1" x 2"
	Dimensions	1 in H x 2 in W
	Height	1 in
	Width	2 in
	Label/Tape Size	1 in H x 2 in W
	Thickness	0.004 in
	Vertical Repeat	1.125 in

Material Characteristics		B-434 (View Technical Data Sheet)
		Metallized Polyester
	Material Properties	Metallic Appearance
	Label Properties	Metallic Labels, Permanent Adhesive Labels
	Adhesive Type	Permanent Acrylic
	Finish	Gloss
	Color	Silver
	Resistance Properties	Abrasion-Resistant, Humidity-Resistant, UV-Resistant, Weather-Resistant
	Minimum Service Temperature °F	-40 °F
	Maximum Service Temperature °F	194 °F
	Compatible Surface Types	High Surface Energy

Downloaded from Arrow.com.

Product Features		Asset Tracking, General Identification, Inventory and Inspection Labeling
	Shape	Rectangle
	Label/Media Format	Roll
	Ribbon Series	R6000HF
	Quantity per Row	1

Printing Specifications	**Print Technology**	Thermal Transfer

Compatibility	**For Use with Printer**	BBP®81 Label Printer, BRADY IP® Series Label Printer, BradyPrinter i5100, BradyPrinter i7100, BRADYPRINTER PR Plus Series Label Printer, THT 3" Core Printer
		IP-R6000, R6006

Compliance		55121612

Related Items

We use cookies to ensure you get the best experience on our website. Learn More.

GOT IT!

Downloaded from Arrow.com.