



Part Number : 1731110297

Product Description : FCT Plastic Backshell for D-Sub Connector, Shielded, Shell Size 3, 90° Angle (or Straight) Cable Outlet, Flat Body, with Grip Cover and #4-40 Locking Screws, Individual Packing

Series Number : 173111


Status : Active

Product Category : D-Sub Backshells

Engineering Number : FPHGR-3AFRE

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant with Exemption 6(a)-I per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	D-Sub Backshells

Series	173111
Description	FCT Plastic Backshell for D-Sub Connector, Shielded, Shell Size 3, 90° Angle (or Straight) Cable Outlet, Flat Body, with Grip Cover and #4-40 Locking Screws, Individual Packing
Magnetic	Yes
Product Family	FCT D-Sub Connectors
Product Name	FCT Products
Type	Plastic
UPC	191128339865

Electrical

Shield Type	Shielded Plastic
Shielded	Yes

Physical

Cable Diameter	max. 11.20mm
Material - Backshell	PC+ABS
Material - Screw	Steel
Mounting Style	Locking Screw
Net Weight	23.000/g
Orientation	Straight or 90° Angle
Packaging Type	Bag
Plating - Backshell	Nickel
Temperature Range - Operating	-35° to +95°C
Thread Size	4-40 UNC
Tightening Test Torque	40 Ncm
Waterproof / Dustproof	No

Use with Part(s)

Description	Part Number
Use With	FCT D-Sub, Size 3

This document was generated on Jul 28, 2024