T 3363 300 U





Data Overview

Description:	Female Receptacle; Front Mount; 5 Pin; Dip Solder 15mm; Silver; IP40
rated voltage	300 V
number of positions (w/o PE)	5
rated current (40 °C)	7 A
termination	DIP
contact plating	silver
IP-class mated	IP40
Product Availability	Currently not on stock
Packing Unit:	**105 Pieces**
Min. Order Quantity:	**105 Pieces**
Price per Piece:	**€3.51**
Total Price plus VAT:	**€368.55**

Send Request

105 Add to Cart

Stock of our Distributors

Technical Data

General Characteristics

part category	female receptacle
gender	female
locking system	screw coupling
assembly of receptacle	single hole front assembly
lower temperature	-40 GC
upper temperature	100 GC
IP-class mated	IP40

Electrical Characteristics

Further Characteristics

Downloads

Frequently Asked Questions

- Which components belong to a complete bill of materials (BOM)?
- Amphenol as a supplier of complete assemblies and plug & play solutions
- What options are there for direct transfer to a printed circuit board?
- How does the transmission of the cable shielding work with M16A connectors?
- Crimping or soldering - what are pros & cons?
- Tarnishing of silver-plated contacts - what's the reason?
- What options are there for color adjustments to the application?
- M16 receptacles with hex nut instead of ring nut?
- What are the 5 and 7 pole stereo layouts used for?
- What does the U at the end of the part number stand for?

This might interest you



Accessory »

Disclaimer: No liability is accepted for the correctness and completeness of the suggested accessories.

Newsletter

E-Mail

I would like to receive the newsletter on the latest products, current trade fairs and promotions and give the following consent.

Subscribe to Newsletter

© Amphenol Tuchel Industrial GmbH 2026

Downloaded from Arrow.com.