


Part Number : [358250211](#)

Product Description : 5.00mm Pitch Automotive Horn Female Housing, Vertical, 2 Circuits for 2.28mm Tab

Series Number : 35825

Status : Obsolete

Product Category : Connector Housings



Documents and Resources

Drawings

[358250211_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Obsolete
Category	Connector Housings
Series	35825
Description	5.00mm Pitch Automotive Horn Female Housing, Vertical, 2 Circuits for 2.28mm Tab
Component Type	Housing
Product Name	N/A
UPC	800755998764

Physical

Circuits (maximum)	2
Color - Resin	Black, Yellow
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	5.240/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.00mm
Stackable	No
Temperature Range - Operating	-40° to +120°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
Automotive Filtered Horn Headers	<u>68131</u>

Use with Part(s)

Description	Part Number
Female Terminals	<u>35407</u>
Silicone Rubber Wire Seals	<u>35903</u>

This document was generated on Jun 14, 2026

Obsolete