

Han Compact-gg-M25-SW-Metal



Image is for illustration purposes only. Please refer to product description.

Part number	19 12 708 0411
Specification	Han Compact-gg-M25-SW-Metal
HARTING eCatalogue	https://harting.com/19127080411

Identification

Category	Hoods / Housings
Series of hoods/housings	Han-Compact®
Type of hood/housing	Hood
Description of hood/housing	for Han-Compact® half cable gland With separate PE terminating point for all inserts of size Han-Compact®

Version

Size	Han-Compact®
Version	Top entry
Number of cable entries	1
Cable entry	1x M25
Locking type	Single locking lever
Field of application	Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	12

Material properties

Material (hood/housing)	Zinc die-cast
-------------------------	---------------



Pushing Performance
Since 1945

Material properties

Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	UL 2237 PVVA2.E318390
	CSA-C22.2 No. 182.3 ECBT8.E235076
	CSA-C22.2 No. 182.3 PVVA8.E318390
Approvals	CE
	DNV GL

Commercial data

Packaging size	1
Net weight	180 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140124219
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466