






PRODUCT NUMBER
SEE PART NO. TABLE



POS	A	B	C	POS	A	B	C
2	2.50	5.8	7.3	10	22.50	25.8	27.3
3	5.00	8.3	9.8	11	25.00	28.3	29.8
4	7.50	10.8	12.3	12	27.50	30.8	32.3
5	10.00	13.3	14.8	13	30.00	33.3	34.8
6	12.50	15.8	17.3	14	32.50	35.8	37.3
7	15.00	18.3	19.8	15	35.00	38.3	39.8
8	17.50	20.8	22.3	16	37.50	40.8	42.3
9	20.00	23.3	24.8				

NOTES:

1. MATERIAL: PA66, UL 94V-0.
2. THIS HSG IS USED WITH FCI RECEPTACLE TERMINAL 10142802.
3. THIS RECEPTACLE MATES WITH FCI PLUG 10142799
4. PRODUCT SPECIFICATION: GS-12-1407.
5. PACKAGE SPECIFICATION: GS-14-2573.
6. PART NUMBER SCHEME:
10142801- X 0 X XX LF

COLOR CODE:

- 0: NATURAL
- 1: BLACK
- 2: BROWN
- 3: RED
- 4: ORANGE
- 5: YELLOW
- 6: GREEN
- 7: BLUE
- 8: PURPLE
- 9: GREY
- 10: WHITE
- 11: MILKY YELLOW
- 12: BRICK RED
- 13: MILKY WHITE

PIN Counts 02~16
PACKAGING
0: BULK

mat'l. code				surface		tolerance	projection	product family
ltr	ecn	no	dr	date	tolerances unless otherwise specified			WTB
A				TONY 2017-02-16	angles	.X±0.30		
					linear	.XX±0.20	mm	
					XXX	.XXX±0.10	scale N.T.S.	
					dr	TONY_LEN	2017-02-16	
					engr	TONY_LEN	2017-02-16	
					chr	ZK_HU	2017-02-16	
					appd	TIM_YAO	2017-02-16	
					sheet	revision	A	
					index	sheet	1	

Amphenol
FCI

10142801

5

B