



Datasheet for part number NEMHMSB-67PGNC-001B

Our Catalog Part Number: NEMHMSB-67PGNC-001B
Our Global Manufacturing Part Number: 078335-0020
Brand: Cannon Product Category: Circular Product Line: Nemesis Series: NEMESIS

Product Datasheet	
SERIES	Nemesis High Mating
COUPLING STYLE	Snap-on / Breakaway
SHELL STYLE	Plug
CONTACT ARRANGEMENT	7 contacts
CONTACT TYPE	Pogo Pin
ORIENTATION	Normal
CODING IDENTIFICATION	blue
TERMINATION TYPE	Crimp Contacts
CABLE LENGTH	1 metre length of cable
CABLE TYPE	7 Way Cable (standard or customer specified)
FINISH	Black Electroless Nickel
WIRE SIZE	24-32 AWG
CONTACT RATING	2 Amps continuous / 3 Amps Peak
VOLTAGE RATING	50 Vdc
INSULATION RESISTANCE	5,000 Mohm min.
DIELECTRIC WITHSTAND VOLTAGE	500 Volts
OPERATING TEMPERATURE	-55°/+125°
CONTACT RESISTANCE	15 mOhm max
VIBRATION	20 g's in accordance with MIL-STD-1344 Method 2005, Condition IV
SHOCK	50 g's in accordance with MIL-STD-1344 Method 2004, Condition E
DURABILITY	10,000 cycles
RECEPTACLE MOUNTING	Tamper proof jam nut
EMI SHIELDING	50db attenuation 100Mhz to 1000Mhz in terminated condition
BOOT	Cable dependant, either overmoulded or adhered
SEALING	IP67
SHELL TO SHELL RESISTANCE	<20 mOhm
BLIND MATE	yes
SNAP ON / BREAKAWAY FORCES	Designed to withstand a 10Kg pull off force minimum
SHELL MATERIAL	Stainless Steel
INSULATOR MATERIAL	Liquid crystal polymer
SEALING MATERIAL	Fluorosilicone rubber
CONTACT MATERIAL	Copper alloy with gold over nickel plating

Specifications and dimensions subject to change.