



CABLE ASSEMBLIES

PLUGGABLE I/O CABLE ASSEMBLIES



Preliminary

TE CONNECTIVITY (TE)

MICROQSFP TO MICROQSFP, 2M 33AWG

[microQSFP](#) | [microQSFP](#)

2821236-3

TE Internal Number: 2821236-3

[EU RoHS Compliant](#)

[EU ELV Compliant](#)

Cable Assembly Type Pluggable / Direct Attach

Wire Size (AWG) 33

Cable Assembly Length (m) 2

Color Black

Flammability Rating CL2

PRODUCT DRAWING

English

3D PDF

DOCUMENTATION

Product Drawings

CABLE ASSEMBLY MICRO QSFP TO MICRO QSFP 32 AWG

PDF

English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Catalog Pages/Data Sheets

EEPROM Map EDR Straight Assembly

PDF

English

MicroQSFP Brochure

PDF

English

MicroQSFP Cable Assembly Technical Datasheet

PDF

English

EEPROM Map MicroQSFP Straight Assembly

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Cable Assembly Type Pluggable / Direct Attach

Connector Type (End A) microQSFP

Connector Type (End B) microQSFP

Cable Style Madison TurboTwin - Round Jacketed

Latching Style Pull Tab Release

Cable Assembly Category High Speed

Product Type Cable Assembly

Configuration Features

Number of Positions 8-Pair

Number of Signal Positions 16

Configuration Double-Ended

Electrical Characteristics

Impedance (Ω) 100

Signal Characteristics

Data Rate (Gb/s) 25

Body Features

Color Black

Dimensions

Wire Size (AWG) 33

Cable Assembly Length (m) 2

Operation/Application

Halogen Free No

Industry Standards

Flammability Rating CL2

Statement of Compliance

Statement of Compliance

PDF
