

Especificaciones



Eaton BSPMA3600WYGR

Eaton Bussmann series BSPM series surge arrester, Technology type MOV, 347/600V, Surge arrester, Thermoplastic, UL94V5, 50/60 Hz, 200 Kilo Ampere, Thermoplastic, Remote Contact

General specifications	
PRODUCT NAME	Eaton Bussmann series BSPM series surge arrester
CATALOG NUMBER	BSPMA3600WYGR
UPC	051712709101
PRODUCT LENGTH/DEPTH	2.13 in
PRODUCT HEIGHT	3.54 in
PRODUCT WIDTH	2.56 in
PRODUCT WEIGHT	0.73 lb
COMPLIANCES	Contact factory RoHS Compliant
CERTIFICATIONS	UL 94V0 UL Listed



Especificaciones del producto	
TYPE	Surge arrester
SPECIAL FEATURES	Technology type MOV
APPLICATION	Surge Protection
FREQUENCY RATING	50/60 Hz

Recursos

NOMINAL DISCHARGE CURRENT	20 kA
OPERATING VOLTAGE	510
VOLTAGE RATING	347/600 V
ENCLOSURE	Thermoplastic, UL94V5
SURGE CURRENT	200 kA
INDICATOR TYPE	Remote contact
SHORT-CIRCUIT RATING	200 kA
OPERATING TEMPERATURE	-35 to 85 °C
MOUNTING METHOD	35 mm DIN rail
DEGREE OF PROTECTION	IP20
MATERIAL	Thermoplastic

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
FECHA:



Eaton Corporation plc
Eaton House
Carretera 30 Pembroke
Dublín 4, Irlanda
Eaton.com

© 2025 Eaton. Todos los
derechos reservados.

Eaton es una marca registrada.
Todas las demás marcas
comerciales son propiedad de sus
respectivos propietarios.

Follow us on social media to get the latest
product and support information.

