



REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LE313A0308	2013-10-15	Raison	Modify Gasket Note.and H Cut
C	LEN1440095~97	2014-04-04	Tom_gu	Change H Cut To D Cut



Cable Length(L):100~1000mm

RCP-5SPFFP-SCM7BXX

XX: 100~1000mm
10: 100mm
15: 150mm
20: 200mm
95: 950mm
A0: 1000mm



Cable length	Tolerance
0.0~100 mm	±10 mm
101~300 mm	±15 mm
301~1000 mm	±20 mm

Note:

- * $\varnothing$ Important Dimension
- * Waterproof Rate : IP67 Mated
- * Housing : Nylon+GF,UL 94V-0,BLACK
- * Screw Nut : Nylon+GF,BLACK
- * $\triangle$ Gasket : Silicone,UL 94V-0,Gray.
- * PCB: FR-4
- * Jack : PBT Polyester UL 94V-0
- * $\triangle$ Use without Waterproof cap or Dust cap
For Panel Thickness Max: 4.2mm
- * Use with Waterproof cap or Dust cap
For Panel Thickness Max: 3.0mm
- * $\triangle$ Screw torsion value range: 8~12kgf-cm

Shield	Drain Wire	接地線	Shield	
8	Brown	棕	8	
7	White/Brown	白/棕	7	Twist
6	Green	綠	6	
5	White/Blue	白/藍	5	Twist
4	Blue	藍	4	Twist
3	White/Green	白/綠	3	
2	Orange	橘	2	Twist
1	White/Orange	白/橘	1	
Jack	Wire Color	Plug		
Pin Out				

Recommended Panel Cut-out Rear View

ALTW
CONFIDENTIAL
2014-04-04
R&D DEPT.

UNIT:mm		TITLE RJ45,C SIZE,MATED WATERPROOF
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°	SCALE 1:1	SIZE A4
	REV. C	SHEET 1 OF 1
	WC-REV. B.4	$\varnothing$ Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Tom_gu	DATE 2014-04-04
DWG NO RCP-5SPFFP-SCM7BXX	CHECKED BY Tony	DATE 2014-04-04
CUSTOMER ALTW	APPROVED BY Victor	DATE 2014-04-04