

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO CW INDUSTRIES INCORPORATED AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE OTHER THAN CW INDUSTRIES PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM CW INDUSTRIES INCORPORATED, SOUTHAMPTON, PENNSYLVANIA USA.


DIMENSIONS IN INCHES (MILLIMETERS)
DO NOT SCALE DRAWING .....

Dwg. No. GRS-4012-0047

PANEL PIERCING







UL, CSA & VDE LISTED:

16A 125–250VAC 3/4H.P. 125–250VAC
3A 125V L 10A 14V(T)
10(4) 250 ~ μ T85°

MATERIALS:

BUTTON & HOUSING– NYLON 6/6 94V–2, COLOR/ BLACK
TERMINAL & MOVING CONTACT – COPPER ALLOY

REVISIONS		
0	RELEASED. DGW 8–01–94 RBK AUG. 5, 1994	
1	REDRAWN. UPDATED WITH NEW FORMAT AND ADDED UL & CSA & VDE LISTED AND MATERIALS. DGW 2–25–2013	FEB 26 2013

B–FORMAT 2002

PDF MADE

CW INDUSTRIES
Southampton, Pa. 18966

TOLERANCES UNLESS OTHERWISE SPECIFIED	
2 Place Decimal ±.010	METRIC
3 Place Decimal ±.005	1 Place Dec. ±.25mm
Angles ..... ±1°	2 Place Dec. ±.13mm

Made for: CW IND.
Drawn by: DGW 8–01–94
Checked by: G. Gucd 2-26-13
Approval: C. Hamm 2/26/13

Title: ROCKER SWIDGET ASSEMBLY (POP–IN) S.P.– D.T.

Division: SWITCH

Dwg. No. GRS-4012-0047

MASTER

Downloaded from Arrow.com.