




JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
EW48	14.0	.040	.150	1.89	16,000	C-2V
EW07	14.0	.080	.300	3.77	15,000	C-2V
EW10	14.0	.100	.500	6.29	10,000	C-2F
EW33	14.0	.125	.700	9.00	10,000	C-2F
EW37	14.0	.125	.700	9.00	10,000	C-2V
EW89	14.0	.140	.880	11.00	14,000	C-2F
EW87	14.0	.140	.950	12.00	14,000	C-2V

THIRD ANGLE PROJECTION			METRIC		DIMENSIONS ARE IN MILLIMETERS		JKL COMPONENTS CORPORATION	
			TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0 ANGLE +/- 0		TITLE T-1 1/2 STANDARD WIRE TERMINAL LAMP			
DRAWN BY L. WENGSTROM			APPV'D BY DATE BW 02/18/00		SIZE A	FSCM NO. 55335	DRAWING NO. WIRE TERMINAL T-1 1/2	
RELEASED 2/18/00			- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SCALE NONE	RELEASED DATE 02/18/00	REVISION DATE	REV. NO.
REV. NO.	DESCRIPTION/ECO NUMBER		APPV'D DATE		1 OF 1			