

PDU Power Cord, C13 to C14 - 10A, 250V, 18 AWG, 2 ft. (0.61 m), Black, 5-Pack

MODEL NUMBER: P004-002-5



Computer power extension cords connect 2 devices with C13/C14 power connectors or extend your existing power connection by 2 ft.

Features

**C14-to-C13 Power Cables Connect Computers, Printers, Servers and Other Equipment**This package of five IEC-320-C14 to IEC-320-C13 cables is designed for small data center, office workstation and other lower-amp applications. These C14 male to C13 female cords can be used to power computers, servers and monitors; attach routers and drives to a UPS system or PDU; or extend existing connections up to 2-ft. (0.61 m). The 2-ft. (0.61 m) length helps reduce cable clutter and minimize the risk of tripping.

Highlights

- Recommended for powering computers, printers and other essential peripherals
- Add 2-ft. (0.61 m) to your existing connection to provide more flexibility in placing devices
- C13-to-C14 PDU-style extension cords are ideal replacements for worn-out or missing cable

Applications

- Connect devices like computers, servers and routers to a PDU up to 2-ft. (0.61 m) away in your data center
- Extend existing power connections up to 2-ft. (0.61 m) to more easily place devices or reach a power source near your workstation
- Provide high-quality replacements for worn-out or missing power cords

Package Includes

- (5) C14 Male to C13 Female Power Cables, 2-ft. (0.61 m), Black

Specifications

| OVERVIEW                    |                                                   |
|-----------------------------|---------------------------------------------------|
| UPC Code                    | 037332142863                                      |
| Device Compatibility        | Computer; Monitor/HDTV; Printer; Server; UPS; PDU |
| Country/Region              | Global                                            |
| INPUT                       |                                                   |
| Maximum Input Amps          | 10                                                |
| Voltage Compatibility (VAC) | 100-250                                           |
| PHYSICAL                    |                                                   |
| Plug Color                  | Black                                             |
| Cable Jacket Color          | Black                                             |
| Cable Jacket Material       | PVC                                               |

|                                      |                                     |
|--------------------------------------|-------------------------------------|
| Cable Jacket Rating                  | FT2                                 |
| Power Cord Jacket Type               | SJT                                 |
| Cable Outer Diameter (OD)            | 7.7mm                               |
| Number of Conductors                 | 3                                   |
| Wire Gauge (AWG)                     | 18                                  |
| Wire Gauge (OD - mm <sup>2</sup> )   | 0.82                                |
| Cable Length (ft.)                   | 2                                   |
| Cable Length (m)                     | 0.61                                |
| Shipping Dimensions (hwd / in.)      | 14.17 x 11.80 x 0.50                |
| Shipping Dimensions (hwd / cm)       | 35.99 x 29.97 x 1.27                |
| Shipping Weight (lbs.)               | 1.10                                |
| Shipping Weight (kg)                 | 0.50                                |
| <b>ENVIRONMENTAL</b>                 |                                     |
| Operating Temperature Range          | -4° to 140°F (-20° to 60°C)         |
| Storage Temperature Range            | -4° to 140°F (-20° to 60°C)         |
| Operating Humidity Range             | 20% to 80% RH                       |
| Storage Humidity Range               | 20% to 80% RH                       |
| <b>CONNECTIONS</b>                   |                                     |
| Side A - Connector 1                 | IEC-320-C14                         |
| Side B - Connector 1                 | IEC-320-C13                         |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                                     |
| Antibacterial                        | No                                  |
| Angled Plug                          | No                                  |
| High Voltage                         | Yes                                 |
| Locking Plug                         | No                                  |
| Coiled Power Cord                    | No                                  |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                                     |
| Product Certifications               | CSA (Canada); cUL Listed; UL Listed |
| Product Compliance                   | RoHS; REACH                         |
| <b>WARRANTY &amp; SUPPORT</b>        |                                     |
| Product Warranty Period (Worldwide)  | Lifetime limited warranty           |



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States



© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.