



WX1012 Kit 120V

Item No: WX1012N

1-Channel Soldering Station, 200 W

KEY FEATURES

- + High Powered Digital Soldering Stations WX 1
- + Capacitive glass touch screen is chemical and temperature resistant
- + Turn and click wheel with enter key and finger guide is intuitive to use
- + Multi-language menu , ready for automation using RS232 Serial I/O commands
- + Large graphic LCD display can be viewed from all angles
- + Acts as a benchtop controller for the WHP1000 / WHP3000 hot plates
- + Acts as a benchtop controller for the Zero Smog 4V / 6V Filtration units
- + Multi-purpose USB port for parameter configuration and DATA LOGGING
- + Compatible with all WX series soldering pencils

TECHNICAL DATA

Length	6.6 in
Dimensions L x W x H	170.0 x 151.0 x 130.0mm
Automatic Tool Identification	Yes
Benchtop Controller	Yes
Equipotential Bonding Socket	Via 3.5mm pawl socket on back of device
ESD Safe	Yes
Interface	1x USB, 2x RS232, 1x Switching Output
Multilingual Display	Yes
Number of Channels	1
Power	200 W
Temperature Accuracy °C	± 9°C
Temperature Accuracy °F	± 17°F
Temperature Range (Depends on Tool)	Adjustable from 50°C - 550°C (150°F - 999°C) Adjustable temperature range varies among tools
Temperature Range °C	100 - 550 °C
Temperature Range °F	200 - 999 °F
Temperature Stability °C	± 2°C
Temperature Stability °F	± 4°F
Tip Range	XNTA (T0054485199)
Tip Type	WX XTNA
Traceability	Yes
UPC	037103305077
USB	USB interface of firmware updates, parameterization and monitoring USB interface supports all standard USB flash drive types
Voltage	120V
Weight (Catalog)	3.20 kg
Product Family	WX Line Soldering Stations