

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0747523051

Status:

Active

Overview:

SFP+ Passive Cable Assembly

Description:

SFP+ Passive Cable Assembly, 10Gbps, 26 AWG Cable, Pull-to-Release Plunger Style Latch, 0.50m Length



Series image - Reference only

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Agency Certification	
UL	E72548
General	
Product Family	Cable Assemblies
Series	74752
Assembly Configuration	Dual Ended Connectors
Comments	Meets customer requirements for speeds up to 10 Gbps. Passive cables may require host pre-emphasis and equalization to reach at the longer lengths.
Connector to Connector	SFP Plus-to-SFP Plus
Overview	SFP+ Passive Cable Assembly
Product Name	SFP Plus
UPC	800756659503
Physical	
Cable Length	0.50m
Circuits (Loaded)	TWO DIFFERENTIAL PAIR
Gender	Male-Male
Lock to Mating Part	Yes
Material - Metal	Beryllium Copper, Zinc Alloy
Net Weight	65.733/g
Packaging Type	Bag
Single Ended	No
Waterproof / Dustproof	Yes
Wire Insulation Diameter	N/A
Wire Size AWG	26
Wire/Cable Type	Twin-ax
Electrical	
Impedance	100Ω
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	3.3V
Material Info	
Reference - Drawing Numbers	
Sales Drawing	747520001-000, SD-74752-001

EU ELV

Not Relevant

EU RoHS

Not Relevant

China RoHS

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Not Relevant

Need more information on product
environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

74752 Series

Mates With

74441 SFP Plus (SFP+) Host Connector

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION