



Representative Image

Catalog No. TC375

Description: STAND-OFF BRKT MTG BASE 3.65IN NAT

UPC No 5414363058779

Home > Wire & Cable Management > Ty-Rap > Cable tie mounts

Stand-Off Brackets Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 92.71mm (3.65 Inches), Width of 17.5mm (0.69 Inches), Height of 19.05mm (0.75 Inches), Screw Mounting Method, Mounting Hole Diameter of 4.8mm (0.189 Inches)

Descriptors

Category	Cable tie mounts
Special Features	These brackets permit bundles to be mounted on either side. They also serve as means to raise bundles off the surface.

Specifications

Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

Classifications

Brand Name	Ty-Rap
------------	--------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant
POPs	POPs 28 Compliant

ETIM	EC000449 Mounting base and -element for cable ties
Length	92.71 mm
Length	3.65 inch
Width	17.5 mm
Width	0.69 inch
Height	19.05 mm
Height	0.75 inch
Type of fastening	Other
Diameter mounting hole	4.8 mm
Material	Plastic

by ABB

ETIM	EC000449 Mounting base and -element for cable ties
Material quality	Polyamide (PA)
Colour	Natural colour