



Part Number : [1200868669](#)

Product Description : Nano-Change (M8) Single-Ended Cordset with Knurled Hexnut, 3 Poles, A-Coded, Female (90°) to Pigtail, 24 AWG, Black TPU WSOR Cable, 5.0m (16.40') Length

Series Number : 120086

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : 403001B41M050



Documents and Resources

Drawings

[1200868669_sd.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | Not Relevant |
| EU ELV | Compliant with Exemption 3 per 2000/53/EC |
| Low-Halogen Status | Not Relevant |
| REACH SVHC | Contains Lead per D(2025)4165-DC (25 June 2025) |
| EU RoHS | Compliant with Exemption 6(c) per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

| | |
|--------------|--|
| Status | Active |
| Category | Circular Industrial Cordsets |
| Series | 120086 |
| Description | Nano-Change (M8) Single-Ended Cordset with Knurled Hexnut, 3 Poles, A-Coded, Female (90°) to Pigtail, 24 AWG, Black TPU WSOR Cable, 5.0m (16.40') Length |
| IP Rating | IP67 |
| Product Name | Nano-Change (M8) |
| Protocol | N/A |
| Type | Single Ended |
| UPC | 889056003742 |

Electrical

| | |
|-------------------------------|-----------------|
| Current - Maximum per Contact | 3.0A |
| Voltage - Maximum | 60V AC / 75V DC |

Physical

| | |
|----------------------|--------------------------|
| Cable Diameter | 4.50mm (.177") |
| Cable Length | 5.0m (16.40') |
| Color - Cable Jacket | Black |
| Connector End A | Nano-Change (M8) |
| Connector End B | Pigtail |
| Coupling Style | Knurled Hexnut, Threaded |
| Gender | Female-Pigtail |

| | |
|-------------------------------|---------------------|
| Keyway | A-Coded |
| LED Indicator | None |
| Material - Cable Jacket | TPU |
| Material - Connector Body | TPU |
| Material - Contact | Brass |
| Material - Coupling Nut | Nickel-plated Brass |
| Material - O-Ring | Fluoro-elastomer |
| Material - Plating Mating | Gold |
| Net Weight | 144.100/g |
| Orientation | 90° to Pigtail |
| Poles | 3 |
| Temperature Range - Operating | -25° to +85°C |
| Wire/Cable Type | UL 21215 |
| Wire Size (AWG) | 24 |

This document was generated on Dec 26, 2025