

WR2002 Set 230V

Item No: T0053380699N
2-Channel Rework Station Set, 200 W (300 W)

KEY FEATURES

- Power unit WR 2, 2 channels with soldering iron WP 80, desoldering iron DSX 80
- Small repair set for all rework applications
- Simultaneous operation of up to 2 soldering tools (hot air and desoldering iron at the same time is not possible)

Downloaded from Arrow.com.

TECHNICAL DATA

Length	10.7 in
Dimensions L x W x H	273.0 x 235.0 x 102.0mm
Automatic Tool Identification	Yes
Capacity (l/min)	18 l/min
Desoldering	Yes
Equipotential Bonding Socket	Via 3.5mm jack bush (initial state-hard-grounded)
ESD Safe	Yes
Hot Air (picto)	Yes
IPC Compliant	(Tip to Ground) Corresponds to IPC-J-001D
Maximum Hot Air Flow Rate l/min (Depends on Tool)	10 l/min
Noise level (distance 1 m) dB(A)	0.7 bar
Number of Channels	2
Overcurrent Release	1,6 A
Power	250 W (300 W)
Temperature Accuracy °C	± 9°C
Temperature Accuracy °F	± 17°F
Temperature Accuracy for Hot Air	± 30°C, ± 54°F
Temperature Stability °C	± 2°C
Temperature Stability °F	± 4°F
UPC	037103305527
Vacuum	0,7 bar
Voltage	230V
Weight (Catalog)	6.70 kg
Product Family	Rework, Hot Air, Desoldering Stations

Downloaded from Arrow.com.