



- NOTES:
1. PARTS TO BE BULK PACKED.
 2. ALL DIMENSIONS ARE REFERENCE ONLY EXCEPT WHERE NOTED WITH TOLERANCE. DIMENSIONS IN BRACKETS [] ARE METRIC.



ASSEMBLED VIEW SHOWN
WITH STANDARD
COUPLING RING



ASSEMBLED VIEW SHOWN
WITH WINGED
COUPLING RING

KIT PART NO.	GROMMET SIZE TO FIT CABLE O.D.
W3280-1XPG-318(W)	0.18 - 0.20 [4.6-5.1mm]
W3280-1XPG-321(W)	0.21 - 0.23 [5.3-5.8mm]
W3280-1XPG-324(W)	0.24 - 0.27 [6.1-6.8mm]
W3280-1XPG-328(W)	0.28 - 0.29 [7.1-7.4mm]
W3280-1XPG-330(W)	0.30 - 0.32 [7.6-8.1mm]
W3280-1XPG-3DC(W)	0.12-0.17-0.24 [3.0-4.3-6.1mm]


(WING COUPLING RING OPTION)

NO. OF CONTACTS

KIT P/N	NO/ OF CONTACTS
W3280-10PG-3XX	(10) - #20
W3280-11PG-3XX	(11) - #20
W3280-12PG-3XX	(12) - #20
W3280-10PG-3XXW	(10) - #20
W3280-11PG-3XXW	(11) - #20
W3280-12PG-3XXW	(12) - #20
ADD W SUFFIX FOR WINGED COUPLING RING OPTION	
W3280-1XPG-3XX(W)	


GROMMET SIZE
SEE P/N LIST

NO. OF CONTACTS



FACE VIEW
W3280-12PG-3XX(W)



O-RING
MAT'L: RUBBER,
BLACK




CABLE INSERT, MALE
MAT'L: UV THERMOPLASTIC,
BLACK




#20 PIN CONTACTS
CRIMP,
GOLD PLATED




GROMMET,
MAT'L: RUBBER,
BLACK
FOR CABLE O.D.
SEE TABLE




SLEEVE
MAT'L: THERMOPLASTIC,
BLACK




BACKSHELL
MAT'L: UV THERMOPLASTIC,
BLACK



WIRE VIEW




FACE VIEW
W3280-10PG-3XX(W)




FACE VIEW
W3280-11PG-3XX(W)

COUPLING RING
MAT'L: UV THERMOPLASTIC,
BLACK


COUPLING RING, WINGED (OPTION)
MAT'L: UV THERMOPLASTIC,
BLACK



CONTACT
INSERTION VIEW



ASSEMBLED VIEW SHOWN
WITH STANDARD COUPLING RING



ASSEMBLED VIEW SHOWN
WITH WINGED COUPLING RING

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____

DATE: _____

A	PAK	8/13/19	DRAWING CREATED & RELEASED PER DOR 10-2523JS-1	
REV.	INIT.	DATE	DESCRIPTION	
	PAK	09/23/14	ORIG. DRAWN BY: DATE: 09/23/14	
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			CHECKED BY:	
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.			APPROVED BY:	
UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16			SCALE NTS	SIZE B
CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			SHEET 1 OF 1	DIRECTORY: SLW
			FILE: W3280-1XPG-3XX	PART NUMBER: W3280-1XPG-3XX(W)
			TITLE: CABLE CONNECTOR KIT #20 PIN CONTACTS (CRIMP) MULTI-CON-X, E-KEY, WEATHER RESISTANT STANDARD PRODUCT	
			REV A	

conxall
601 E. WILDWOOD VILLA PARK, IL 60181

TITLE: CABLE CONNECTOR KIT
#20 PIN CONTACTS (CRIMP)
MULTI-CON-X, E-KEY, WEATHER RESISTANT
STANDARD PRODUCT

PART NUMBER: W3280-1XPG-3XX(W)

REV A