





Minimum cable diameter: $\phi F_{max} = 3$
 Maximum cable diameter:
 - with rubber bushing: $\phi F_{max} = 6,5$
 - without rubber bushing: $\phi F_{max} = 8,5$
 - without reduction plate: $\phi F_{max} = 12,5$

09670250334	4-40UNC
Part number	screw thread

		All Dimensions in mm Original Size DIN A4		Scale 1:1		Free size tol.		Ref.	
		All rights reserved		Created by DOUGE		Inspected by BAGDIKIAN		Standardisation KOHLER	
Department EC PD - FR								Date 2013-01-29	
HARTING Electronics GmbH								State Final Release	
D-32339 Espelkamp								Doc-Key / ECM-Nr. 100521735/UGD/001/A 500000056836	
								Rev. A	
								Page 1/1	