





MICRO SWITCH
a Honeywell Division

FED.MFG.CODE 91929

MINIATURE PRECISION LIMIT SWITCH

CATALOG LISTING

914CE18-AQ




NOTES

- 1 - ZINC HOUSING FINISHED WITH GRAY PAINT
- 2 - SIDE EXIT CONNECTOR

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE	FULL	DO NOT SCALE PRINT
		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
OPERATING FORCE — — — — 5 LB MAX	CONTACT ARRANGEMENT S P D T	ONE PLACE	(.0)	±.030
DIFFERENTIAL TRAVEL — — — .004 MAX		TWO PLACE	(.00)	±.015
OVERTRAVEL — — — — .118 MIN	5A 1/10HP — 125 OR 250 VAC	THREE PLACE	(.000)	±.005
		ANGLES		±
		WEIGHT		



914CE18-AQ

M

DRAWING
NUMBER

1

ISSUE

REPLACES

CO-69061

RELEASE NO.

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

DDM/CAD

DRAWN

SAV

11 OCT 91