



[Home](#) ▶ [1N3477 \(#2078\)](#)

Products

- ▶ [Product Directory](#)
- ▶ [Applications Directory](#)
- ▶ [Parametric Search](#)

1N3477 (#2078)

Overview

Diagrams

Shipping TR14

Electrical Rating	Symbol	Min	Typ	Max	Unit
Regulator voltage, reference voltage (dc)	V _Z			2.20	V

Maximum Electrical Rating	Symbol	Min	Typ	Max	Unit
Power Dissipation, Total	P _T			0.25	W
Tolerance	Tol			10.00	%

This part can be found in the following product categories:

▶ [Discretes](#) ▶ [Diodes](#) ▶ [Zener](#) ▶ [Zener Voltage Regulator Diode](#)

Related Links

- [Technical support](#)
- [Sales Contacts](#)**
- [Available Stock](#)
- [Sales Contacts](#)
- [RFQ/Samples](#)