Part Number : 731711290
Product Description : BNC Plug, Straight, Crimp, RG-179 Cable, Brass Body, Nickel (Ni) Plated, 75 Ohms
Series Number : 73171
Status : Active
Product Category : RF / Coaxial Connectors



Documents and Resources

Drawings

731711290_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 3; 33; 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73171
Description	BNC Plug, Straight, Crimp, RG-179 Cable, Brass Body, Nickel (Ni) Plated, 75 Ohms
Application	RF
Product Name	BNC
Style	Cable
Type	Miniature
UPC	800756008639

Electrical

Frequency	4 GHz
Impedance	75Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level

Physical

Cable Attachment	Crimp
Gender	Plug
Keying to Mating Part	N/A
Net Weight	7.685/g
Orientation	Straight
Packaging Type	Bag
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	N/A
Reverse Polar	No

Downloaded from Arrow.com.

Wire/Cable Type	RG-179

This document was generated on Oct 16, 2026

Downloaded from Arrow.com.