



Global - English

Web Site Optoelectronics Stock Check

ProductsApplicationsDocumentationAbout UsWhere to BuyInvestor RelationsNews & EventsContact Us

Request more info

Part Number : 5988410207CF







This is a
RoHS Compliant Product
To learn more click here

General Description








Lamp Type	Bi-Color
Lens Color	Non-Diffused
MSL	3
Compliance	EIA-481-1
Series	598
Configuration	0606(1.6MM X 1.6MM X 0.7MM)
Description	SMD LED 0606 PACKAGE, BI-COLOR
Package Options	Tape and Reel

Absolute Maximum Ratings (Ta = 25°)

Forward Current mA	20mA
Reverse Current	10 μ A@ Vr = 5V
Forward Current Pulsed	100mA
Derating	from 25°C = .42mA/°C
Solder Temperature	260° for 10 sec
Operating Temperature	-40~+100
Storage Temperature	-40~+100
ESD	2000

Operating Characteristics

LED Type	AlInGaP
Color	Bi-Color (Red and Green)





Copyright © 2013, Dialight. All Rights Reserved.