Part Number : 2079125520
Product Description : High-Speed FAKRA Mini (HFM) Single Plug Housing, 1x1, Key A, Black, with Clipslot
Series Number : 207912
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

2079125520_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

2079110012-000.pdf

2088700000PS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 47; 34
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

Downloaded from Arrow.com.

- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	207912
Description	High-Speed FAKRA Mini (HFM) Single Plug Housing, 1x1, Key A, Black, with Clipslot
Application	Automotive, RF, Wire-to-Wire
Component Type	Housing
Product Name	High-Speed FAKRA Mini (HFM)
UPC	195842833227

Physical

Circuits (maximum)	1
Color - Resin	Black
Durability (mating cycles max)	25
Gender	Male
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polybutylene Terephthalate (PBT)
Net Weight	1.663/g
Number of Rows	1

Downloaded from Arrow.com.

Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	N/A
Pitch - Termination Interface	N/A
Polarization	A
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
High-Speed FAKRA Mini (HFM) Single Jack Housing, 1x1, Key A, Black, with CPA	2079118120
High-Speed FAKRA Mini (HFM) Single Jack Housing, 1x1, Key A, Black, without CPA	2079118140

Use with Part(s)

Description	Part Number
High-Speed FAKRA Mini (HFM) Plug Inner Contact, for RTK031 Coaxial Cable, Gold (Au) Plating	2079122000
High-Speed FAKRA Mini (HFM) Plug Outer Contact, for RTK031 Coaxial Cable, Tin (Sn) Plating	2079123000
High-Speed FAKRA Mini (HFM) Plug Inner Contact, for RG174 Coaxial Cable, Gold (Au) Plating	2079122001
High-Speed FAKRA Mini (HFM) Plug Outer Contact, for RG174 Coaxial Cable, Tin (Sn) Plating	2079123001
High-Speed FAKRA Mini (HFM) Crimp Sleeve, for RTK031 Coaxial Cable, Tin (Sn) Plating	2079113402
High-Speed FAKRA Mini (HFM) Crimp Sleeve, for RG174 Coaxial Cable, Tin (Sn) Plating	2079113401

Downloaded from Arrow.com.

Downloaded from Arrow.com.