Part Number : 745460403
Product Description : iPass PCIe x4 Cable Assembly, 28 AWG, 3.0m Length
Series Number : 74546
Status : Obsolete
Product Category : High-Speed I/O Cable Assemblies



Documents and Resources

Drawings

745460403_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Obsolete

Downloaded from Arrow.com.

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	High-Speed I/O Cable Assemblies
Series	74546
Description	iPass PCIe x4 Cable Assembly, 28 AWG, 3.0m Length
Assembly Configuration	Dual Ended Connectors
Connector to Connector	PCI Express-to-PCI Express
Product Name	iPass,PCI Express
Type	Pluggable
UPC	822348864843

Agency

CSA	LR64395
UL	E72548

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	30V DC

Physical

Cable Bundling	None
Cable Length	3.0m
Circuits (Loaded)	38
Circuits (maximum)	38
Gender	Male-Male
Lock to Mating Part	Yes
Material - Metal	Zinc Alloy
Net Weight	575.000/g
Packaging Type	Bag
Release Style	Pull Tab
Single Ended	No

Obsolete

Downloaded from Arrow.com.

Waterproof / Dustproof	Yes
Wire/Cable Type	Round
Wire Insulation Diameter	N/A
Wire Size (AWG)	28

Mates With / Use With

Mates with Part(s)

Description	Part Number
iPass I/O Right-Angle Surface Mount Receptacles	75586

Use with Part(s)

Description	Part Number
PCIe Guide Frames	74540

This document was generated on Sep 15, 2026

Obsolete

Downloaded from Arrow.com.