






TYPE I

类型 I




Single PG/M thread
单个 PG/M螺纹孔



TYPE 2

类型 2


Two PG/M threads
两个 PG/M螺纹孔



All dimension is same as TYPE I, except those defined in this TYPE
除了在本类型中定义的尺寸外，其他尺寸同类型 I

NOTES:
1. TECHNICAL CHARACTERISTICS:
HOOD MATERIAL: DIE CAST ALUMINIUM ALLOY
SURFACE: SEE TABLE
DEGREE OF PROTECTION: IP68 (MATED)

注释
1. 技术参数:
壳体材料: 铝合金
表面处理: 见表格
防护等级: IP68 (配合)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 08OCT2016 DAVID WANG	 TE Connectivity			
DIMENSIONS:		CHK 08OCT2016 CHRIS WANG				
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD 08OCT2016 XIANG XU	NAME H16BPR-TGHC-PG/M-EMC-C			
	0 PLC	±	PRODUCT SPEC 108-137191			
	1 PLC	±	APPLICATION SPEC 114-137191			
	2 PLC	±	WEIGHT -			
	3 PLC	±	Customer Drawing			
MATERIAL	4 PLC	±	SIZE A2			
-	ANGLES	±	CAGE CODE -			
-	FINISH	-	DRAWING NO. T192216XXXXX09			
			RESTRICTED TO -			
			SCALE 1:1 SHEET 1 OF 2 REV C			

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

NOTES:

SEE SHEET 1


备注:

见 SHEET 1

T1922160225-009	H16BPR-TGHC-2M25-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY 2M25,BLACK H16BPR上壳,中部锁定,顶出2M25,黑色	M25	M25	-	TYPE 2 类型2
T1922162150-009	H16BPR-TGHC-M50-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY M50,GREY H16BPR上壳,中部锁定,顶出M50,灰色	-	-	M50	TYPE 1 类型1
T1922161140-009	H16BPR-TGHC-M40-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY M40,SILVER WHITE H16BPR上壳,中部锁定,顶出M40,银白色	-	-	M40	
T1922161136-009	H16BPR-TGHC-PG36-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY PG36,SILVER WHITE H16BPR上壳,中部锁定,顶出PG36,银白色	-	-	PG36	
T1922161132-009	H16BPR-TGHC-M32-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY M32,SILVER WHITE H16BPR上壳,中部锁定,顶出M32,银白色	-	-	M32	
T1922161129-009	H16BPR-TGHC-PG29-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY PG29,SILVER WHITE H16BPR上壳,中部锁定,顶出PG29,银白色	-	-	PG29	
T1922161125-009	H16BPR-TGHC-M25-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY M25,SILVER WHITE H16BPR上壳,中部锁定,顶出M25,银白色	-	-	M25	
T1922161121-009	H16BPR-TGHC-PG21-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY PG21,SILVER WHITE H16BPR上壳,中部锁定,顶出PG21,银白色	-	-	PG21	
T1922160140-009	H16BPR-TGHC-M40-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY M40,BLACK H16BPR上壳,中部锁定,顶出M40,黑色	-	-	M40	
T1922160136-009	H16BPR-TGHC-PG36-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY PG36,BLACK H16BPR上壳,中部锁定,顶出PG36,黑色	-	-	PG36	
T1922160132-009	H16BPR-TGHC-M32-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY M32,BLACK H16BPR上壳,中部锁定,顶出M32,黑色	-	-	M32	
T1922160129-009	H16BPR-TGHC-PG29-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY PG29,BLACK H16BPR上壳,中部锁定,顶出PG29,黑色	-	-	PG29	
T1922160125-009	H16BPR-TGHC-M25-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY M25,BLACK H16BPR上壳,中部锁定,顶出M25,黑色	-	-	M25	
T1922160121-009	H16BPR-TGHC-PG21-EMC-C	H16BPR HOOD,CENTER LOCKING,TOP ENTRY PG21,BLACK H16BPR上壳,中部锁定,顶出PG21,黑色	-	-	PG21	
PART NUMBER 料 号	DESCRIPTION 描 述		PG/M THREAD-3 PG/M 螺纹-3	PG/M THREAD-2 PG/M 螺纹-2	PG/M THREAD-1 PG/M 螺纹-1	TYPE 类型

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL
-

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±-

2 PLC ±-

3 PLC ±-

4 PLC ±-

ANGLES ±-

FINISH -

-

DWN 08OCT2016
DAVID WANG

CHK 08OCT2016
CHRIS WANG

APVD 08OCT2016
XIANG XU

PRODUCT SPEC
108-137191

APPLICATION SPEC
114-137191

WEIGHT
-

Customer Drawing

TE Connectivity

NAME
H16BPR-TGHC-PG/M-EMC-C

SIZE
A2

CAGE CODE
-

DRAWING NO
T192216XXXXX09

RESTRICTED TO
-

SCALE 1:1SHEET 2 OF 2REV C

1471-9 (3/13)

Downloaded from Arrow.com