

**Part Number :** [936014687](#)

**Product Description :** Heavy-Duty Standard (STD) Single Lever Bulkhead Mount Housing, Polyamide, with 1 Lever, Side Entry, with Cable Gland, Size «32x13», Pg21 Thread, Black

**Series Number :** 93601

**Status :** Active

**Product Category :** Heavy-Duty Connectors

**Engineering Part Number :** 7908.6664.1



---

## Documents and Resources

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

## Part Details

### General

Status	Active
Category	Heavy Duty Connectors
Series	93601
Description	Heavy-Duty Standard (STD) Single Lever Bulkhead Mount Housing, Polyamide, with 1 Lever, Side Entry, with Cable Gland, Size «32x13», Pg21 Thread, Black
Component Type	Single Lever Bulkhead Housing
IP Rating	IP66, IP67
Product Name	Heavy-Duty Connectors
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191842677

### Agency

CSA	256883
UL	E249674

### Electrical

Voltage - Maximum	500V
-------------------	------

### Physical

Cable Diameter	11.00-18.00mm
Component Size	«32X13»
Entry Location	Side
Gland Color	Black RAL 9005
Housing Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Cable Gland	Polyamide

Material - Housing	Polyamide
Material - Lever	Polyamide
Mounting Style	Bulkhead
Net Weight	46.000/g
Number of Levers	1
Packaging Type	Bag
Thread Size	Pg21
Thread Type	(Pg)

## Mates With / Use With

### Use with Part(s)

Description	Part Number
Use With	Size «32x13» S-QD Inserts

---

This document was generated on May 19, 2026