






PART NUMBER	CABLE O.D. RANGE
S15KS20	Ø 0.205 - 0.225 [5.21 - 5.72]
S15KS23	Ø 0.235 - 0.255 [5.97 - 6.48]
S15KS26	Ø 0.265 - 0.285 [6.73 - 7.24]

NOTES:

1. RATED 15 AMP, 24 VOLT DC AT 105° C (CURRENT CARRY ONLY) WHEN USING 14 AWG STRANDED CONDUCTOR CABLE.
2. USE CABLE LUBE WHEN ASSEMBLING CABLE.
3. IP68 RATED WHEN MATED TO ST15S JACK.
4. HANDLE SHIPPED UNASSEMBLED.
5. THIS PRODUCT IS ROHS COMPLIANT.

CUSTOMER DRAWING

						THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.												
					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.005 [0.13]	SIZE		WIDTH		MULT		LBS/M		TEMPER				
						FINISH						MATERIAL						
						SPEC No.						SPEC No.						
						FIRST USED ON				SCALE 2:1		Switchcraft®						
						DATE DRAWN		BY	CHKD		APVD							
A	28515	7/18/22	TJK	TJK			5-13-19		SRC	SRC 6-29-22		TJK 7/26/22		SHEET 1 OF 1				
REV	ECO NUMBER	DATE	BY	APVD		NAME						PART No.				REV		
REVISIONS					DO NOT SCALE DRAWING	15 AMP SEALED PLUG, RoHS						S15KS SERIES				A		