



**Part Number :** [1300980131](#)

**Product Description :** MAX-LOC Strain Relief Cord-Sealing Grip w/ O-Ring, 3/4" NPT, 90° Angle Male, Cable Diameter 17.45-20.62mm (.687-.812"), Stainless Steel Mesh

**Series Number :** 130098

**Status :** Active

**Product Category :** Cable Grips

**Engineering Number :** 5545W



---

## Documents & Resources

---

### Product Environment Compliance

#### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

#### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Cable Grips
Series	130098
Description	MAX-LOC Strain Relief Cord-Sealing Grip w/ O-Ring, 3/4" NPT, 90° Angle Male, Cable Diameter 17.45-20.62mm (.687-.812"), Stainless Steel Mesh
NEMA Rating	NEMA 6P
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678855452

### Agency

CSA	LR32159
UL	E76954

### Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	90° Angle
Cable Diameter	17.45-20.62mm (.687-.812")
Color - Grommet	Yellow
Eye Type	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	N/A
Mesh Length	N/A
Number of Holes	1
O-Ring	Yes
Thread Size	3/4" NPT

### Mates With / Use With

**Use with Part(s)**

Description	Part Number
MAX-LOC Lock Nut 3/4" NPT	<u>1300990144</u>

---

This document was generated on Sep 17, 2025