



+ RELAYS, CONTACTORS & SWITCHES
DC



✓ Active

TE CONNECTIVITY (TE)
E311TS1=RELAY
Hartman

E311TS1
TE Internal Number: 8-1616960-9

- Not EU RoHS Compliant
- Not EU ELV Compliant
- Contact Arrangement SPST NC
- Contact Current Rating (A) 3, 5
- Coil Voltage (Max) (VDC) 100
- Coil Voltage Rating (VDC) 100
- Coil Termination 6-32 UNF-2A

↓ PRODUCT DRAWING
English

DOCUMENTATION

Product Drawings
E311TS1=RELAY
PDF
English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.
Please Note: Use the Product Drawing for all design activity.

Product Type Features

Terminal Configuration 6-32 UNF-2A
Contactors Type Sealed
Product Category Electromechanical Relays
Product Type Contactor
Product Classification Relays - Contactors
Arc Cover Without

Electrical Characteristics

Coil Voltage (Max) (VDC) 100
Coil Voltage Rating (VDC) 100
Actuating System DC

Contact Features

Contact Arrangement SPST NC
Contact Current Rating (A) 3, 5
Number of Poles 1

Termination Features

Coil Termination 6-32 UNF-2A

Mechanical Attachment

Mounting Type Chassis
Mounting Plate With

Other

Torque (in-lbs) 7.5 in-lbs

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance
PDF