

## Honeywell Sensing and Control

Search

**LSXYPB3K**

( Home : Products : Switches &gt; MICRO SWITCH™ Hazardous Location Switches &gt; LSX )



Explosion-Proof Limit Switches LSX Non Plug-in: Low Temperature Version; Side Rotary; 1NC 1NO SPDT Snap Action; 0.5 in - 14 NPT conduit

*Actual product appearance may vary.***narrow your search**

## Products

- Controls Monitoring and Lighting ( 286 )
- Machine Safety ( 1727 )
- Sensors ( 6158 )
- Switches ( 9781 )
- Wireless ( 45 )

## Technology

- Control and Instrumentation ( 890 )
- Electromechanical ( 9303 )
- Magnetic ( 538 )
- Platinum thin film ( 56 )
- Thick Film ( 1372 )
- More...

**new products****New Wireless Products**

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.

Wireless Web Site  
WGLA and WPMM  
XYR6000™

find out more

**white papers**

- ▷ Wireless Switches Offer Unlimited Benefit
- ▷ Basic Switches Are Not Created Equal
- ▷ Applying Precision Switches
- ▷ Sensors for Medical Devices
- ▷ New Ways to Measure Torque
- ▷ Choosing Safety Switches
- ▷ Specifying Hour Meters

**Need help?**

Click here to contact us

**LSXYPB3K**

( Home : Products : Switches > MICRO SWITCH™ Hazardous Location Switches > LSX )



*Actual product appearance may vary.*

**Sales & Service**

**Distributor Inventory**

[Overview](#)
[Specs](#)
[Documentation](#)
[Application Notes](#)

**Product Specifications**

Availability	Global
Operating Force (OF)	0.45 Nm [4 in lb] max.
Pretravel (PT)	9° max.
Overttravel (OT)	66° min.
Differential Travel (DT)	3° max.
Product Type	MICRO SWITCH™ Weather-Sealed, Explosion-Proof Limit Switches
Actuator	Side Rotary
Lever Type	Lever Not Included - Reference Lever Required Accessory
Circuitry	1NC 1NO SPDT Snap Action, Double-Break
Ampere Rating	10 A (Thermal)
Supply Voltage	600 Vac and 250 Vdc max.
Housing Material	Zinc Die-Cast
Termination Type	0.5 in - 14 NPT Conduit
Housing Type	LSX Non Plug-in
Series Name	LSX
Sealing	NEMA 1, 3, 4, 6, 7 (Class 1, Division 1, Groups B, C, D), 9 (Class 2, Division 1, Groups E, F, G), 13
CSA File #	LR57327
UL File #	E61730
Operating Temperature	-40 °C to 121 °C [-40 °F to 250 °F]
Comment	Low Temperature Construction; Maintained contact
Agency Approvals and Standards	UL, CSA
UNSPSC Code	302119
UNSPSC Commodity	302119 Switches and controls and relays
Sealed	Explosion-proof

**contacts**

- ▷ Customer Service
- ▷ Technical Support
- ▷ Global Sales & Service
- ▷ View Site Demo
- ▷ Site Comments ?

**meet dr. larry**

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



Meet Dr. Larry

**my links**

- ▷ Login to iCOM
- ▷ Login to Rep/AD Portal
- ▷ Login to Digital University

**News Center**

- ▷ HONEYWELL INTRODUCES TRUSTABILITY® NSC SERIES, UNCOMPENSATED / UNAMPLIFIED BOARD MOUNT PRESSURE SENSORS
- ▷ HONEYWELL EXPANDS ITS LIMITLESS™ PLATFORM WITH THE LAUNCH OF ITS GLOBALLY AVAILABLE INDUSTRIAL WIRELESS RECEIVER
- ▷ HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION

**MICRO SWITCH Anniversary site**

Terms &amp; Conditions | Privacy Statement | Site Map