

240V Corded UPS Backplate Outlet Kit for
SU6000RT3, L6-30R, L6-20R, 5-15/20R

MODEL NUMBER: SUPDM13



Highlights

- Converts Tripp Lite's hardwire SU6000RT3U UPS systems to one with AC plug and outlets
- For use with 240V UPS output voltage configurations
- 10 ft. / 3m AC input power cable with NEMA L6-30P input plug
- 1 L6-30R, 2 L6-20R and 10 5-15/20R output receptacles
- Easy quick-connect wiring installs in minutes

Description

Tripp Lite's SUPDM13 corded backplate kit converts Tripp Lite's hardwire SU6000RT3U UPS system into one with AC plug and outlets. 10 ft./3m input line cord with L6-30P plug enables simple connection to 240V 30A mains power. Includes 1 L6-30R, 2 L6-20R and 10 5-15/20R output receptacles. Easy quick-connect wiring installs in minutes.

VOLTAGE COMPATIBILITY NOTE - SUPDM13 supports SU6000RT3U applications configured for 240V nominal input voltage only (See SUPDM12 for 208V input voltage configurations).

Features

- Converts Tripp Lite's hardwire SU6000RT3U UPS system to one with an AC plug and outlets
- 10 ft./3m AC line cord with L6-30P input plug-in connection
- Includes 1 L6-30R, 2 L6-20R and 10 5-15/20R output receptacles
- Easy quick-connect wiring installs in minutes

Specifications

OVERVIEW	
UPC Code	037332120847
Accessory Type	Backplate Outlet Kit
Accessory Class	UPS Accessories
INPUT	
Nominal Input Voltage(s) Supported	208V AC

UPS Input Cord Length (ft.)	10
UPS Input Cord Length (m)	3.1
Recommended Electrical Service	30A 240V
Input Connection Type	NEMA L6-30P input plug
Voltage Compatibility (VAC)	208
OUTPUT	
Output Receptacles	(10) 5-15/20R; (2) L6-20R; (1) L6-30R
Output Nominal Voltage	Simultaneous 240 and 120V output
Overload Protection	120V outlets are protected by 2 separate 20A branch rated circuit breakers
PHYSICAL	
Material of Construction	Steel
Shipping Dimensions (hwd / in.)	5.00 x 13.50 x 9.10
Shipping Dimensions (hwd / cm)	12.70 x 34.29 x 23.11
Shipping Weight (lbs.)	5.60
Shipping Weight (kg)	2.54
Unit Dimensions (hwd / in.)	3.500 x 5.000 x 11.000
Unit Dimensions (hwd / cm)	6.4 x 12.7 x 28
Unit Weight (lbs.)	6
Unit Weight (kg)	2.72
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty