

Data Sheet | Item Number: 261-361

End plate; with fixing flange; gray

<https://www.wago.com/261-361>



Color: ■ gray

Physical data

Width	3 mm / 0.118 inches
Height	18 mm / 0.709 inches
Depth	28 mm / 1.102 inches

Material data

Note (material data)	Information on material specifications can be found here
Color	gray
Material group	I
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.03 MJ
Weight	1.1 g

Environmental requirements

Processing temperature	-35 ... +85 °C
Continuous operating temperature	-60 ... +105 °C

Commercial data

Product Group	9 (Std Chassis Mt Blocks)
PU (SPU)	300 (50) pcs
Packaging type	Box
Country of origin	CH
GTIN	4017332141260
Customs tariff number	85389099990



Product Classification	
UNSPSC	39121702
eCl@ss 10.0	27-14-11-33
eCl@ss 9.0	27-14-11-33
ETIM 9.0	EC000886
ETIM 10.0	EC000886
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Downloads

Environmental Product Compliance

Compliance Search	
Environmental Product Compliance 261-361	↓

Documentation

Bid Text			
261-361	19.02.2019	xml 2.55 KB	↓
261-361	17.08.2017	doc 23.00 KB	↓

CAD/CAE-Data

CAD data	
2D/3D Models 261-361	↓

CAE data	
EPLAN Data Portal 261-361	↓
WSCAD Universe 261-361	↓
ZUKEN Portal 261-361	↓

1 Compatible Products

1.1 Optional Accessories

1.1.1 Installation

1.1.1.1 Mounting accessories



Item No.: [209-123](#)

Mounting foot with screw; can be screwed on terminal blocks with fixing flange; 6.4 mm wide; gray