

PRODUCT TOP

CATEGORY

SPECIFICATIONS

INDUSTRIES

SERIES NAME

Enter Keyword, Product name or HRS code.

SEARCH

Product Top > MMCX series > MMCX-LP-178B/U(40)



RoHS2

- ▶ [Product Numbers by Series](#)
- ▶ [Part Number Configuration](#)

MMCX-LP-178B/U(40)

Product	MMCX-LP-178B/U(40)
Series	MMCX
Connector Type	Plug
Generic Type	MMCX
Cable Assembly	No
Characteristic Impedance	50 Ω

Detailed Specifications

Last Updated On Oct. 19, 2017

▼ Product information	
Part No.	MMCX-LP-178B/U(40)
CL No.	CL0339-0001-7-40
▼ Basic information	
Connector Type	Plug
Generic Type	MMCX
Cable Assembly	No
Characteristic Impedance	50 Ω
Frequency (Max.)	6 GHz
Number of Positions	1
Mating/Unmating Cycles	500
Connector Orientation	Right angle
Center Contact Plating	Gold
Outer Contact Plating	Gold
Recommended Coaxial Cable	RG-178B/U
Operating Temperature	-55 to 85 °C
▶ Mechanical Specifications	

Download

DRAWING(2D)

DRAWING(3D)

▶ more

ADD TO MY LIST



CONTACT US

Browsing History



Series: [MMCX](#)
Product: [MMCX-LP-178B/U\(40\)](#)

Download

Catalog	Product Series Catalog	↓ DOWNLOAD
Data Sheet	Drawing (2D)	↓ DOWNLOAD
	3D Model (IGES)	↓ DOWNLOAD
	3D Model (STEP)	↓ DOWNLOAD
	Specification Sheet	↓ DOWNLOAD

*I [need help](#) with a product or information

[Product Top](#)

[About Us](#)

[Specifications](#)

[Industry](#)

[Series Name](#)

[Partners](#)

[Global Site](#)

[Privacy Policy](#)

[Terms of use](#)

[Membership Agreement](#)



© 1999-2018 HIROSE ELECTRIC CO., LTD. All Rights Reserved.

SUPPORT

[FAQ](#)

[CONTACT US](#)

