
Data Sheet | Item Number: 756-1604/060-020

sercos cable; M12D plug; angled; M12D plug; angled; 4-pole; Length: 2 m


https://www.wago.com/756-1604/060-020






Color: red

Similar to illustration





Dimensions in mm

Short description:

- PUR RD, halogen-free
- CAT 5e ES
- Suitable for drag chains
- Silicon- and CFC-free
- High resistance to microbes, hydrolysis, oil, ozone, chemicals and UV radiation
- Cable used: UL listed

Technical data	
Operating voltage	250 V
Insulation resistance	≥ 5 x 10^8 Ω/km
Conductor resistance	< 57 Ω/km

Downloaded from Arrow.com.

Mechanical data

Weight	160 g
Color	red

Commercial data

PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4050821591238
Customs tariff number	85444290900
End of Sale	2024-05-01
End of Production	2024-05-15
End of Delivery	2024-06-01
End of Service and Repair	2025-06-01

Product Classification

UNSPSC	26121609
eCl@ss 10.0	27-06-18-01
eCl@ss 9.0	27-06-18-01
ETIM 9.0	EC002599
ECCN	NO US CLASSIFICATION

Approvals / Certificates

General approvals

Approval	Standard	Certificate Name
UL Underwriters Laboratories Inc.	UL 1863	E345416

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance
756-1604/060-020

Downloaded from Arrow.com.

Documentation

System Description

I/O-SYSTEM – SPEED-WAY, General Product Information	pdf 1035.20 KB	↓

CAD/CAE-Data

CAE data

WSCAD Universe 756-1604/060-020	↓

Downloaded from Arrow.com.