

75904-02 DPST Master Disconnect Switch

With two Hencol keys.

Two positions: Off-On.

For 6-36V DC systems.

Will disconnect the battery and the alternator or generator field circuit.

Electrical ratings: Large studs: 1000A intermittent. 15 seconds On, 5 minutes Off. 125A continuous.

Small studs: 20A continuous.

Plated steel case.

Silver-laminated contacts.

Brass mounting stem 3/4" -16 thread 17/32" (13.5mm) long. Fits panels through 1/4" (6.4mm) thick.

Two 3/8" -24 and two 10-32 studs.

With indexing pin.



Specifications

Description	Master Disconnect Switch
Details	Double Pole, Two Positions: Off-On
UL listed	not listed
Rating	6-36V DC; Large studs 125A continuous - 1000A intermittent, 15 sec. On, 5 min. Off; Small studs 20A continuous
Terminals	two 3/8" copper studs, two 10-32 studs
Actuators	"Hencol" lock with two keys
Mounting stem	brass, 3/4" - 16 thread, 17/32" long, fits panel through 1/4" thick
Case	plated steel, with indexing/alignment pin
Installation	Through holes - Clearance for 3/4" dia. mounting stem and index pin
Contacts	silver laminated

Related Products

83353
Hencol Key

Commercial Vehicle Products
20 Old Colony Avenue
Boston, MA 02127-2467, USA
+1 617.268.2100