



**Part Number :** [334722060](#)

**Product Description :** MX150 Mat-Sealed Female Connector Assembly, Dual Row, 20 Circuits, Keying Option C, without Connector Position Assurance, Dark Gray

**Series Number :** 33472

**Status :** Active

**Product Category :** Connector Housings



---

## Documents and Resources

### Drawings

[334722060 sd.pdf](#)

[PK-31300-903-001.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[AS-33472-100-001.pdf](#)

[AS-33472-100-CH-001.pdf](#)

[AS-33472-100-FR-001.pdf](#)

[AS-33611-001-001.pdf](#)


[PS-33472-000-001.pdf](#)

[TS-33472-0001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21

REACH SVHC	Contains Dodecamethylcyclohexasiloxane; Decamethylcyclopentasiloxane; Octamethylcyclotetrasiloxane per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Connector Housings
Series	33472
Description	MX150 Mat-Sealed Female Connector Assembly, Dual Row, 20 Circuits, Keying Option C, without Connector Position Assurance, Dark Gray
Application	Power, Wire-to-Board, Wire-to-Wire, Automotive
Product Name	MX150
UPC	884982301962

### Agency

UL	E29179
----	--------

## Physical

Circuits (maximum)	20
Color - Resin	Gray (Dark)
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	21.495/g
Number of Rows	2
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +150°C

## Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
MX150 2x10 Dual Row Right-Angle Header, 20 Circuits, Keying Option C, Dark Gray, Solder Tail	<a href="#"><u>348302003</u></a>
MX150 Mat-Sealed Dual Row Male Connector Assemblies	<a href="#"><u>33482</u></a>

### Use with Part(s)

Description	Part Number
MX150 Sealed Receptacle Cavity Plug	<a href="#"><u>343454001</u></a>
MX150 Female Terminals	<a href="#"><u>33001</u></a>
MX150 Female Terminals	<a href="#"><u>33012</u></a>

---

This document was generated on Apr 30, 2026