

## CompactFlash Cards CompactFlash 800

Professional photographers and videographers needing to capture fast action in continuous burst mode or record lengthy Full HD video footage can count on Transcend's CompactFlash 800 cards to deliver the speed and capacity necessary to do the job. Back in the studio, the CompactFlash 800 cards ensure quick and easy transfer of card content to your computer so you can spend more time on photo retouching and video editing. Additionally, the top-tier MLC NAND flash chips inside are durable and reliable.



### A trusted choice

Transcend's CompactFlash 800 memory cards are manufactured with top-tier MLC NAND flash memory, making them durable and reliable. Ideal for use with advanced cameraholders and mid-range to high-end DSLR cameras for landscape, portrait, and event photography, these cards come in particularly handy during continuous burst mode shooting and lengthy Full HD and 3D video recording, offering professional photographers and videographers impressive transfer rates and stable video recording without dropping frames.




### Shoot at amazing transfer speeds

Transcend's CompactFlash 800 memory cards meet the VPG-20 (Video Performance Guarantee) standard to ensure a sustained minimum write speed of 20MB/s. With read/write speeds of up to 120MB/s and 60MB/s respectively, you can enjoy lag-free, professional-grade Full HD and 3D video capture.



### Get larger storage capacity

With up to 256GB storage capacity, Transcend's CompactFlash 800 memory cards allow tens of thousands of photos or hundreds of hours of Full HD videos to be recorded. Supporting UDMA7 (high-speed Ultra DMA transfer mode 7), the cards offer not only prompt response during fast-action burst mode shooting, but also fast storage of high-resolution images in the RAW format. Stay focused on capturing crucial moments, and let the memory card handle the rest.



## CompactFlash Cards

# CompactFlash 800

## Features

- Supports Ultra DMA Mode 7
- Features Video Performance Guarantee-20 (VPG-20)
- Up to 256GB storage capacity
- MLC NAND flash



### RecoveRx

RecoveRx is a data recovery software for memory cards, USB flash drives, external hard drives and SSDs.

## Specifications

### Appearance

Dimensions	42.8 mm x 36.4 mm x 3.3 mm (1.69" x 1.43" x 0.13")
Weight	11.4 g (0.4 oz)

### Storage

Capacity	32 GB / 64 GB / 128 GB / 256 GB
Flash Type	MLC NAND flash

### Operating Environment

Operating Temperature	-25°C (-13°F) ~ 85°C (185°F)
Operating Voltage	3.3V ~ 5V

### Performance

Read Speed (Max.)	up to 120 MB/s
Write Speed (Max.)	up to 60 MB/s
Insertion/Removal Cycles	10,000

### Warranty

Certificate	CE / FCC / RCM / EAC
Warranty	Five-year Limited Warranty

## Ordering Information

32GB	TS32GCF800
64GB	TS64GCF800
128GB	TS128GCF800
256GB	TS256GCF800

Product specifications are subject to change without notice. Pictures shown may differ from actual products. Total accessible capacity varies depending on operating environment.