

**Part Number :** [351500614](#)

**Product Description :** VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Blue

**Series Number :** 35150

**Status :** Active

**Product Category :** Connector Housings



---

## Documents and Resources

### Drawings

[351500614\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[351500000AS\\_ENG-000.pdf](#)

[351500000AS\\_KOR-000.pdf](#)


[PK-35150-005-001.pdf](#)

[PS-35150-003-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Connector Housings
Series	35150
Description	VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 6 Circuits, Blue
Application	Power, Wire-to-Wire
Product Name	VersaBlade
UPC	800754834889

### Agency

CSA	LR19980
UL	E29179

### Physical

Circuits (maximum)	6
Color - Resin	Blue
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	No
Lock to Mating Part	Yes

Material - Resin	PBT
Net Weight	6.160/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	7.30mm
Pitch - Termination Interface	7.30mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +120°C

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
VersaBlade Hybrid Plug Housings	<a href="#">35151</a>

### Use with Part(s)

Description	Part Number
VersaBlade Terminal Position Assurance (TPA) Retainer, 7.30mm Pitch, 3 Circuits, Natural	<a href="#">351500390</a>
VersaBlade Terminal Position Assurance (TPA) Retainer, 7.30mm Pitch, 3 Circuits, Red	<a href="#">351500392</a>
VersaBlade Terminal Position Assurance (TPA) Retainer, 7.30mm Pitch, 3 Circuits, Yellow	<a href="#">351500393</a>
VersaBlade Terminal Position Assurance (TPA) Retainer, 7.30mm Pitch, 3 Circuits, Blue	<a href="#">351500394</a>
VersaBlade Male Crimp Terminal, 24-22 AWG, Type C	<a href="#">2270288400</a>
VersaBlade Female Crimp Terminal, 24-22 AWG, Type C	<a href="#">2270298400</a>
VersaBlade Male Crimp Terminals	<a href="#">35745</a>
VersaBlade Female Crimp	<a href="#">35746</a>

Terminals	
VersaBlade Male Crimp Terminals	<u>35747</u>

---

This document was generated on Apr 15, 2026