

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -




ALL RIGHTS RESERVED.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED AS PER ECR-15-005925	21APR2015	RS	JL
	A1	REVISED AS PER ECR-15-009215	19JUN2015	RS	JL

NOTES:

- 1 MATERIALS:
CONTACTS: COPPER ALLOY, TIN PLATE
CONTACT POSITIONER: GLASS FILLED PBT,
COLOR BLACK.
2. MUST COMPLY WITH DIRECTIVE 2002/95/EC (ROHS)
3. CONTACTS (3X) ARE PRE-ASSEMBLED INTO CONTACT
POSITIONER AS SHOWN.
- 4 ASSEMBLY "KEY" ALIGNS WITH "PE"
CONTACT AS SHOWN.
5. THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING



IEC (DEKRA)	1-2213427-1
UL	2213427-1
AGENCY APPROVALS	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. SHAFFER 31MAR2014	 TE Connectivity	
		CHK M. LUKSIC 31MAR2014		
DIMENSIONS:		APVD M. LUKSIC 31MAR2014	NAME	
mm		PRODUCT SPEC	ASSY, FI SOCKET, NECTOR M-LINE	
		108-133014	SEALED, 3 POSN	
		APPLICATION SPEC	-	
MATERIAL		114-32111	SIZE	RESTRICTED TO
		WEIGHT	A3	-
		Customer Drawing	SCALE	REV
			1:1	A1