


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS				
BD	39	P	LTR	DESCRIPTION	DATE	DWN
			B1	REVISED PER ECO-06-020813	30OCT06	JDP
						APVD
						CWR

OPENING FOR CABLE
(SEE DASH NO FOR DIA)



SIZE IDENTIFICATION
LETTER MOLDED HERE
(SEE TABLE)

#4-40 FILLISTER HEAD
STEEL SCREW
& HEX NUT, ZINC
PLATED, 2 REQD.



.620 ± .015

.620 ± .015

CABLE CLAMP
MATERIAL: FLAME RETARDANT THERMOPLASTIC
FINISH: BRIGHT NICKEL OVER BRIGHT COPPER

#4-40 FILLISTER HEAD SCREW
STEEL, ZINC PLATED, 2 REQD.

- 1
- ALL PARTS PACKAGED UNASSEMBLED.
- 2
- AS SHOWN ABOVE, THIS KIT CONSISTS OF 2
STRAIN RELIEF HALVES, 2 #4-40 SCREWS, 2 #4-40 NUTS &
2 #4-40 MOUNTING SCREWS.
- 3
- SAME AS SHOWN, EXCEPT: EACH PART IS INDIVIDUALLY BULK
PACKED FOR MULTIPLE KIT ORDERS.
- 4
- OBSOLETE

1	B	.225	4	747099-8		747099-7
	E	.300	4	747099-6	4	747099-5
	H	.375	4	747099-4	4	747099-3
	K	.430	4	747099-2	4	747099-1
REMARKS	SIZE IDENT LETTER	CABLE DIA	BULK PACKED KIT NO	3	INDIVIDUAL KIT NO	2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	J	GALLUCCI	BG	5-16-90	tyco Electronics		Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: INCHES		CHK			APVD	NAME		CABLE CLAMP KIT, SIZE 2, 15 POSN, 180 DEGREE AMPLIMTE				
		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		APPLICATION SPEC		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± ±		— — — — —		— — — — —		A200779		C-747099		—
MATERIAL SEE CALLOUT		FINISH SEE CALLOUT		WEIGHT		CUSTOMER DRAWING		SCALE		SHEET	REV	
				—				2:1		1 of 1	B1	