

Part Number : [513470650](#)

Product Description : 3.30mm Pitch Wire-to-Board Receptacle Housing, Positive Lock, Single Row, 6 Circuits, White

Series Number : 51347

Status : Obsolete

Product Category : Connector Housings

Documents and Resources

Drawings


[513470650 sd.pdf](#)

Specifications

[PS-51284-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Connector Housings
Series	51347
Description	3.30mm Pitch Wire-to-Board Receptacle Housing, Positive Lock, Single Row, 6 Circuits, White
Application	Signal, Wire-to-Wire
Product Name	N/A
UPC	822348218264

Physical

Circuits (maximum)	6
Color - Resin	Natural
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1171.000/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.30mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-25° to +85°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
3.30mm Pitch Wire-to-Board Header, Single Row, with Positive Lock, 6 Circuits	<u>558830659</u>

Use with Part(s)

Description	Part Number
3.30mm Pitch Terminal Position Assurance (TPA) Retainers	<u>51348</u>
3.30mm Pitch Female Crimp Terminals	<u>56187</u>

This document was generated on Apr 12, 2026

Obsolete