



**Part Number :** [936010477](#)

**Product Description :** Heavy-Duty Turned Crimp Contact for 5A D-Sub Inserts and Modules, Female, Gold (Au) Plated Copper Alloy, 0.14-0.35mm<sup>2</sup> (26-22 AWG), 100 per Bag

**Series Number :** 93601

**Status :** Active

**Product Category :** Heavy-Duty Contacts

**Engineering Part Number :** 7700.3437.1



---

## Documents and Resources


### Drawings

[936010477\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

## UKCA - Declaration of Conformity

## CE - Declaration of Conformity

---

## Part Details

### General

Status	Active
Category	Contacts
Series	93601
Description	Heavy-Duty Turned Crimp Contact for 5A D-Sub Inserts and Modules, Female, Gold (Au) Plated Copper Alloy, 0.14-0.35mm <sup>2</sup> (26-22 AWG), 100 per Bag
Contact Type	Turned Crimp
Product Name	Heavy-Duty Connectors
UPC	887191892856

### Electrical

Current - Maximum per Contact	5.0A
-------------------------------	------

### Physical

Gender	Female
Material - Contact	Copper Alloy
Material - Plating	Gold
Net Weight	0.210/g
Number of Grooves	0
Packaging Type	Bag
Stripping Length	5.00mm
Wire Size (AWG)	22, 24, 26
Wire Size mm <sup>2</sup>	0.14-0.35

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
GWconnect Heavy-Duty Connectors and Accessories	<u>93601</u>

### Use with Part(s)

Description	Part Number
Use With	D-Sub Connectors

---

This document was generated on Jan 05, 2026