



- Circuit Board Indicators
- Panel Mount Indicators
- Solid State Lighting
- Traffic Signals
- Vehicle Lighting
- Rail
- Obstruction Lighting
- Hazardous Area Lighting
- Heliport Lighting

- how to purchase
 -  sales contacts
 -  stock check

 search

 Product Line Search

Please select a Product Line to search.

Circuit Board Indicators

find

☐ Part # / Text Search

Part No.:

Text Search:

- quick links
- Dialight Corporate Video
 - Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)
- Application Notes
FAQs
- Dialight Ltd (UK)
Dialight Garufo
Dialight BLP
LumiDrives

Circuit Board Indicators - Through Hole Indicators	
P/N# 5680731111F	3 mm Lens
Description	3 mm Quad Backlighting R/G-R/G-R/G-R/G
Package Options	5 Pieces Per Bag
Product Type	Through Hole Indicators
Sub Product Type	with Quad Level Housing
Configuration	3 mm Lens
Viewing	Right Angle
Viewing Angle	60
Test Current (mA)	10mA
Absolute Maximum Ratings (T _a = 25 °)	
Solder Temp	260Â° for 5 sec
Operating Temp	-55 to +100° C
Storage Temp	-55 to +100° C



Operating Characteristics		
LED Position	Found in position(s): 1-4	
Color	 Red / Green	
Lamp Type	Bi-Color / Bi-Color	
LED Type		
Intensity Min (mcd)	2.5 / 3.7	
Intensity Typ (mcd)	4.7 / 10.0	
Intensity Max (mcd)		
Fwd Voltage Min		
Fwd Voltage Typ		
Fwd Voltage Max		
Dom Wavelength Min (nm)	621 / 569	
Dom Wavelength Typ (nm)		
Dom Wavelength Max (nm)		
Power Dissipation Max (mW)	100 / 100	
Backlighting		
Pitch Between Vertical		
Pitch Between Horizontal		
Lum Intensity Min		
Lum Intensity Typ		
Lum Intensity Max		

Distributor Stock Check

Check stock with our distributors now.

5680731111F

check stock