

Reel Smart™ FSD74-8-K covered single wire Ferrules

FSD74-8-K

Insulated ferrules, single wire turquoise DIN end sleeve on mini-reel, #22 AWG (0.34mm²) Wire Size, 0.31 (8.0mm) Pin Length.

Specifications

Note	Not UL Listed
Ferrule Type	Single Wire Standard
Cover Material	Polypropylene
Copper Conductor Size	22 AWG
Maximum Metric Conductor Size (mm²)	0.34
Wire Strip Length (In.)	13/32
Wire Strip Length (mm)	10
Pin Length (In.)	0.31
Pin Length (mm)	8
Inside Diameter (In.)	0.03
Inside Diameter (mm)	0.8
Maximum Operating Temperature (°C)	105
Maximum Operating Temperature (°F)	221
Maximum Wire Insulation Diameter (In.)	0.07
Maximum Wire Insulation Diameter (mm)	1.8
Outer Diameter (In.)	0.05
Outer Diameter (mm)	1.3
Overall Length (In.)	0.57
Overall Length (mm)	14.5
Product Type	Covered Single Wire Ferrule
Standards Met	DIN 46228 Part 4, CSA C22.2 No. 291-14
Finish/Coating	Tin-Plated
For Use With	CP-881-KIT4
Packaging Type	Bag
Base Material	Copper
Color Code	Turquoise
Sub Brand	Reel Smart™

Downloaded from Arrow.com.

Specifications (continued)

Part Features	Polypropylene insulation housing available in DIN standard colors in reels up to 3000 Designed specifically for use with the Ferrule Applicator (CA10) for high volume applications Continuously molded design provides consistent placement of ferrules in applicator to ensure fast, reliable terminations

Packaging Detail

UPC	07498333337
Std. Pkg. Qty.	1000
Std. Pkg. Volume (cf)	0.0164
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000

Downloaded from Arrow.com.